

## Tec Gun

PROFESSIONAL ERGONOMIC TUBE GUN







High power transfer



# Technical Info Packing Tec Gun for cartridges 18/1 315200000 Tec Gun hand gun for 600ml sausages 12/1 315500000

#### **Product**

#### Characteristics

The Tec Gun is used for squirting most products in the tube, irrespective of the viscosity, and even for two-part products with its 18:1 pump ratio.

The Tec Gun has a pre-tensioning option to enable clean finishing.

The Tec Gun has a pressure rod in stainless steel with suspension hook.

The Tec Gun has a strengthened transmission system.

The Tec Gun is ergonomic in use due to its perfect balance and a turning butt to keep the nozzle in the correct position.

### Use

- · Cut cartridge open and screw on the nozzle.
- · Cut off the nozzle to the required size.
- Place the cartridge in the holder (extractor at the back).
- The black lip on the de-tensioner has two options: downwards for a continuous pressure, recommended when working with hard products such as X-Tack, and upwards for slight withdrawal to limit the running of softer products such as Flex.

